

# Micromax™ 7780

## Electronic Inks and Pastes

### Termination for Trimmers/Potentiometers

Specially developed for trimmer/potentiometer application, Micromax™ 7780 is a silver/platinum termination that meets the needs of low cost and high performances.

### Product characteristics

- High resolution screen printing
- High green strength
- 850 °C/60min. firing
- No Staining
- Good solderability
- High solder leach resistance
- High aged adhesion
- Cadmium, Nickel and Phthalate free\*
- Low cost material

\*Cadmium, Nickel and Phthalate 'free' as used herein means that cadmium, nickel, and phthalate are not intentional ingredients in and are not intentionally added to the referenced product. Trace amount however may be present.

### Product information

Solvent or thinner Micromax™ 8250

### Rheological properties

Viscosity 80 - 150<sup>[1]</sup> Pa.s

[1]: Brookfield HBT, UC&S, 10 rpm, 25 °C ± 1 °C

### Application technique

|                                   |            |
|-----------------------------------|------------|
| Mask mesh                         | 250        |
| Mask emulsion                     | 15 µm      |
| Drying time                       | 10 min     |
| Drying temperature                | 150 °C     |
| Recommended film thickness, dried | 20 - 25 µm |
| Leveling time                     | 5 - 10 min |

### Storage and stability

Shelf life 6<sup>[2]</sup> months

[2]: in unopened containers, from date of shipment, at temperature <25 °C

# Micromax™ 7780

## Electronic Inks and Pastes

### Additional information

How to use

### Processing

- **Substrates**
  - Reported properties are based on tests with 96% alumina substrates.
  - Substrates of other compositions may yield variations in performance properties.
- **Printing**
  - Properties are based on Micromax™ 7780 printed to 20-25µm dried print thickness using 250 mesh stainless steel screen with an emulsion thickness of approximately 15µm.
- **Thinning**
  - Micromax™ 7780 is optimized for screen printing and thinning is not normally required. For minor adjustments, Micromax™ thinner 8250 is recommended.
- **Clean-up solvent**
  - While traditional screen cleaners work with Micromax™ 7780, Axarel® 2200, a non CFC alternative, is recommended.
- **Drying**
  - Prints should be allowed to level at room temperature for 5-10 minutes and then dried for 10 minutes at 150°C.
- **Firing**
  - Properties are based on a 60 minute firing cycle with 10 minutes at a peak of 850°C.

### Properties

- The information given herein is based on data believed to be reliable, but the Micromax™ company makes no warranties expressed or implied as to its accuracy and assumes no liability arising out of its use by others. This publication is not to be taken as a license to operate under, or recommendation to infringe upon, any patents.

### Storage and shelf life

Containers should be stored, tightly sealed, in a clean, stable environment at room temperature (<25°C). Shelf life of material in unopened containers is six months from date of shipment. Some settling of solids may occur and compositions should be thoroughly mixed prior to use.

# Micromax™ 7780

## Electronic Inks and Pastes

### Safety and handling

For safety and handling information pertaining to this product, read Safety Data Sheet (SDS).

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colourants or other additives may cause significant variations in data values. Properties of moulded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Other than those products expressly identified as medical grade (including by MT® product designation or otherwise), Celanese's products are not intended for use in medical or dental implants. Regardless of any such product designation, any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such information. The information contained in this publication should not be construed as a promise or guarantee of specific properties of our products. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to the lowest practical limits in view of possible adverse effects. To the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any equipment, processing technique or material mentioned in this publication should satisfy themselves that they can meet all applicable safety and health standards. We strongly recommend that users seek and adhere to the manufacturer's current instructions for handling each material they use, and entrust the handling of such material to adequately trained personnel only. Please call the telephone numbers listed for additional technical information. Call Customer Services for the appropriate Materials Safety Data Sheets (MSDS) before attempting to process our products.

© 2023 Celanese or its affiliates. All rights reserved. Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC. KEPITAL is a registered trademark of Korea Engineering Plastics Company, Ltd.