

Product Information

## VESTAKEEP® i4 3DF-T

### POLYETHER ETHER KETONE FILAMENT TESTING GRADE DESIGNED FOR RESEARCH, DEVELOPMENT AND PROCESS OPTIMIZATION



**VESTAKEEP® i4 3DF-T** is a filament extruded from natural colored, high viscosity VESTAKEEP® i4 G polyether ether ketone (PEEK) resin. The material is a testing grade designed for research, development and process optimization only. It must not be used for medical devices.

#### Purpose of the testing grade

The purpose of the testing grade is to offer a cost-efficient solution for printing process development.

The testing grade VESTAKEEP® i4 3DF-T and the implantable grade VESTAKEEP® i4 3DF are both extruded from implantable-grade VESTAKEEP® i4 G resin. They share the same base resin, processability and mechanical properties.

#### Delivery of VESTAKEEP® i4 3DF-T

VESTAKEEP® i4 3DF-T filament has a diameter of 1.75 mm (+/- 0.02 mm\*) and is supplied on TROGAMID®-spools in either 250g or 500g. The spools are packaged in double bags to facilitate transfer into clean areas.

The properties listed are for information only and only apply to the VESTAKEEP® i4 G resin used in the manufacture of VESTAKEEP® i4 3DF-T. The performance and the purity of any parts manufactured from VESTAKEEP® i4 3DF-T are highly dependent on any 3D- or additive-printing processes, or any other processing, to which the filament is subjected. Only density and filament diameter apply to VESTAKEEP® Care i4 3DF-T directly.

#### Key Features

##### Industrial Sector

Medical Devices, 3D Printing

##### Processing

3D Printing

##### Delivery form

(Mono)filament

##### Optics

Opaque

##### Resistance to

Heat (thermal stability), Hydrolysis / hot water, Oil / fuels

##### Conformity

Medical application

##### Additives

Unfilled

Mechanical properties ISO	dry	Unit	Test Standard
Tensile modulus	<b>508000</b>	psi	ISO 527
Tensile strength	<b>13600</b>	psi	ISO 527
Yield stress	<b>13600</b>	psi	ISO 527
Yield strain	<b>5</b>	%	ISO 527
Stress at break	<b>11000</b>	psi	ISO 527
Charpy impact strength, +23°C	<b>N</b>	ftlb/in <sup>2</sup>	ISO 179/1eU
Charpy impact strength, -30°C	<b>N</b>	ftlb/in <sup>2</sup>	ISO 179/1eU
Charpy notched impact strength, +23°C	<b>4.33</b>	ftlb/in <sup>2</sup>	ISO 179/1eA
Type of failure	<b>C</b>	-	-
Charpy notched impact strength, -30°C	<b>2.85</b>	ftlb/in <sup>2</sup>	ISO 179/1eA
Type of failure	<b>C</b>	-	-

Thermal properties	dry	Unit	Test Standard
Melting temperature	<b>640</b>	°F	ISO 11357-1/-3
Glass transition temperature, DSC	<b>306</b>	°F	ISO 11357-1/-2
Temp. of deflection under load A, 1.80 MPa	<b>302</b>	°F	ISO 75-1/-2
Temp. of deflection under load B, 0.45 MPa	<b>401</b>	°F	ISO 75-1/-2
Vicat softening temperature A, 10 N, 50 K/h	<b>635</b>	°F	ISO 306
Vicat softening temperature B, 50 N, 50 K/h	<b>581</b>	°F	ISO 306
Melting Temperature	<b>640</b>	°F	ASTM D 3418

Physical properties	dry	Unit	Test Standard
Density	<b>1.3</b>	g/cm <sup>3</sup>	ISO 1183
Filament Diameter	<b>0.0689</b>	in	-
Density	<b>1.3</b>	g/cm <sup>3</sup>	ASTM D 792

Burning Behav.	dry	Unit	Test Standard
Burnin behav. at thickness h	<b>V-0</b>	class	IEC 60695-11-10

Thickness tested	<b>0.1260</b>	in	-
------------------	---------------	----	---

**Rheological properties**

	dry	Unit	Test Standard
Melt volume-flow rate, MVR	<b>12</b>	cm <sup>3</sup> /10min	ISO 1133
Temperature	<b>380</b>	°C	-
Load	<b>5</b>	kg	-

**Characteristics**

**Applications**

Monofilament

**Features**

Resistance to steam

**Processing**

Fused deposition molding, Additive manufacturing

**Color**

Natural color

**Special Characteristics**

Semi-crystalline, High viscosity, Sterilizable

**Chemical Resistance**

Acid resistance, Alkali resistance, Solvent resistance, Grease resistance, Hydrolytically stable, Oil resistance, Oxidation resistance, General chemical resistance

**Other extrusion**

**Drying recommendations**

We recommend to dry the filament prior to usage to avoid stringing, bubbles, or other defects.

- a) Filament on spool: minimum 12 hours at 80°C to 100°C. 100°C must not be exceeded to avoid distortion of the spool.
- b) Filament removed from spool: minimum 4 hours at 130°C to 140°C.

The maximum drying temperature of the filament is 140°C. Please also pay attention to the instructions of your drying device.

**Spool dimensions**

For dimensions of the spool, please see drawing below. All dimensions are given in millimeter (mm).

